Contact-less Dispensing ArcticChill 88 CL

ArcticChill 88 With Contact-less Dispensing

23cm Dispensing Height To Fill Bottles



(Infra Red Sensor)





Delivers 30 - 40 Litres Per Hour Of Chilled Water Below 12°C



refreshingly different

Direct chill cold water cooler

- Infra red sensor to enable contact-less dispensing Keep out of direct or reflected sunlight δ face away from external doors and windows, to avoid activating the sensor Retains blue dispensing button as a manual option Fitted with a 10 Litre overflow kit

- Fits our standard cowling and wall bracket
- WRAS approved
- FloodGuard inlet solenoid protects the cooler against large scale flooding Impressive 23cm dispensing height
- Please read the operating and installation instructions to ensure that the installation site is suitable for contact-less installation

Contact-less Dispensing ArcticChill 88 CL

Accessories For The ArcticChill 88 CL

Filter Housing With Carbon Block Candle & Nanofilter.



Installation Rail With Filter. Includes Compression Fitting, 1-Micron Green Filter, Water Block, Copper Pressure Reducing Valve & Non-Return Valve.



Fittied With Our 10 Litre Overflow System With Alarm To Signal When Full.



Cowling To Fix The Cooler Securely To The Wall (Supplied Separately).



FloodGuard - Inlet Solenoid Only Opens To Allow Water Into The Cooler, When Water Is Dispensed. By Remaining Closed All Other Times It Protects The Cooler Against Leaks.



Mains Drainage - Connect The Drip Tray To Mains Drainage. Can Be Supplied With A Pump, To Pump The Water Over 50m & A Rise Of 5m.



Infra red sensor to enable contact-less dispensing

- Green power LED indicates power is on.
- Orange LED will light up during dispensing.
- To activate dispensing place your hand in front of the sensor <4cm.
- Keep out of direct or reflected sunlight & face away from external doors and windows, to avoid activating the sensor

Description	Dimensions H x W x D mm	Weight (Kg)
POU Floor Standing	1135 x 340 x 340	25

Local Distributor





www.aafirst.co.uk